



## **MOUNTING INSTRUCTION**

**1**

Double-check the motor and gearbox size.  
Clean the mounting surface.

**2**

Remove the plug on the adapter plate.  
Rotate the set collar till the bolt is line up.

**3**

a. Remove motor key.  
b. Insert balance key.

**4**

Check motor shaft size and insert bushing if necessary.

**✓ Correct installation.**  
When installing on flatted shafts, be sure to align the collet gap over the flat and the set collar bolt perpendicular to the flat.

**5**

Set at vertical position. Tighten the mounting bolts (including washer) in 1~4 order with wrench to 5% specified torque. (See Table 1)

**6**

Tighten the set collar bolt with torque wrench to specified torque. (See Table 2)

**7**

Tighten the mounting bolts in 1~4 order with torque wrench to specified torque. (See Table 1)

**8**

Tighten back the screw plug.

**Table 1 Tightening Torque Recommended for Motor Mounting Bolt**

Bolt Size	Width Across Flats	Strength 8.8 Tightening Torque		Strength 10.9 Tightening Torque		Strength 12.9 Tightening Torque	
	[mm]	[Nm]	[In-lbs]	[Nm]	[In-lbs]	[Nm]	[In-lbs]
M3 x 0.5P	2.5	1.3	12	1.8	16	2.1	19
M4 x 0.7P	3	3	27	4.1	37	4.9	44
M5 x 0.8P	4	6.1	55	8.2	73	9.8	87
M6 x 1P	5	11	98	14	124	17	151
M8 x 1.25P	6	25	222	34	302	41	364
M10 x 1.5P	8	49	434	67	594	80	709
M12 x 1.75P	10	85	753	116	1028	139	1232
M14 x 2P	12	137	1214	186	1648	223	1976
M16 x 2P	14	210	1860	286	2534	343	3038

**Table 2 Tightening Torque Recommended for Set Collar Bolt**

Gearbox Size		Motor Shaft Dia.	Bolt Size	Width Across Flats	Tightening Torque	
		[mm]	[mm]	[mm]	[Nm]	[In-lbs]
AT / ATB 065	1 stage	≤11	M3 x 0.5P x 8L	2.5	2.1	19
AT / ATB 075	1 stage	≤14	M4 x 0.7P x 12L	3	4.9	44
AT / ATB 090	1 stage	≤19	M5 x 0.8P x 14L	4	9.8	87
AT / ATB 110	1 stage	≤24	M5 x 0.8P x 14L	4	9.8	87
AT / ATB 140	1 stage	≤32	M6 x 1P x 16L	5	17	151
AT / ATB 170	1 stage	≤38	M8 x 1.25P x 20L	6	41	364
AT / ATB 210	1 stage	≤42	M10 x 1.5P x 25L	8	80	709
AT / ATB 240	1 stage	≤48	M10 x 1.5P x 25L	8	80	709
AT / ATB 280	1 stage	≤55	M12 x 1.75P x 30L	10	139	1232

**Note:** Holding torques must be bigger than values shown above. Bolts can be tightened up to 20% higher for increased holding torques.



**APEX DYNAMICS, INC.**

Tel : 886-4-24650219 / Fax : 886-4-24650118

E-Mail : [sales@apexdyna.com](mailto:sales@apexdyna.com) / Web : [www.apexdyna.com](http://www.apexdyna.com)

NO. 10, Keyuan 3rd Rd., Situn District, Taichung City 40763, Taiwan(R.O.C)